

Introduction

A switching power supply operates from a switching clock source. In systems with multiple switching power supplies, the switching phase between power supplies may need to be manipulated to reduce undesired effects in a system. These undesired effects include large peak current drawn from the input voltage and high levels of radiated emissions due to synchronized edges of the switching frequency. Phase spreading is a method of reducing these effects. Applications of multiple switching power supplies include multi-phase (single rail, current shared) and multi-rail (tracking and Autonomous Sequencing™) designs.

Phase Spreading Types

Phase spreading can be achieved in a number of ways. One type of phase spreading is to allow the switching power supplies to operate individually, from their own internally generated clock. This type of phase spreading effectively randomizes the occurrence of the switching frequency edges, which reduces the chances of high peak currents from the input source. This type will be referred to as “non-coherent phase spreading.”

Another type of phase spreading involves distributing phase edges of each power supply operating from a common switching clock. This type of phase spreading utilizes a single reference clock. All of the power supply devices then use this clock, but each device has its phase set to a different value through out the cycle of the clock. A two-device power supply group may have the phases set 180° from each other. A three-device group may have the phases set to 120° from each other and so on. This type of phase spreading reduces the peak current draw from the input source. It also effectively reduces the magnitude and increases the frequency of radiated emissions.

This type will be referred to as “synchronized phase spreading.”

Synchronized Phase Spreading in the ZL2005

Pin-Strap Configuration

Multiple instances of the ZL2005 are referred to as a “group.” For a group of ZL2005 devices, a single switching clock can be sourced to all devices. Therefore, all devices of the group are synchronized to a single source. This synchronized clock sourcing can be realized by one of two methods. One method of sourcing the switching clock is to supply it from the main system and configure the CFG pin of all ZL2005 devices in the group to set the SYNC pin as an input. The CFG pin configuration definitions are found in the ZL2005 data sheet.

A second method of sourcing the switching clock is to configure a ZL2005 device to source the switching clock. The CFG pin is used to set the sourcing device’s SYNC pin to an output state. The CFG pins of the other devices are then set to configure their SYNC pins to an input state. When using the ZL2005 in a bus sequenced group, the device with no prequel in the group (first device to power-on) must be used as the SYNC output source.

In either method of pin-strap clock sourcing, each device within a group is set to a phase position within the cycle of the sourced clock by virtue of each device’s address pins settings. A device’s address within a group determines the device’s phase position within the group in modulo eight fashion. This means that the address settings of 0x20 through 0x27 will have corresponding phase offsets of 0° for address 0x20, 45° for address

0x21 and so on up to 315° for address 0x27. Other example address ranges for phase spreading are 0x28 through 0x2F, 0x50 through 0x57, or 0x68 through 0x6F. The device address is configured by the SA1:SA0 pins. Refer to the ZL2005 data sheet for the address pins' settings.

Note that for certain group applications, such as Autonomous Sequencing, the device addresses must be set in a consecutive order. This means that the operating phase of each device may not be evenly distributed throughout the cycle of the sourced switching clock. However, the effect of reducing peak current draw will be achieved.

PMBus Configuration

A group of ZL2005s can also be configured for synchronized phase spreading via PMBus commands. As described in the pin-strap configuration section, the ZL2005's SYNC pin can be configured as an input to accept an external switching clock. The USER_CONFIG command is used to perform this setting. The command should be written to set the SYNC pin as an input and to use the source applied to SYNC as the switching clock.

To configure one of the ZL2005 devices of a group to be the source of the switching clock, the USER_CONFIG command is again used. The USER_CONFIG command is written to cause the internal switching signal to drive the SYNC pin as an output. The MFR_CONFIG command should also be considered to set the mode of the SYNC pin when used as an output. MFR_CONFIG can be written to set the pin's operation to open-drain or push-pull.

The PMBus command, INTERLEAVE, can be used to accurately set the position of a device's operational phase. If the INTERLEAVE command is not set (0x0000 default), the address of each device will determine the position of its phase within the switching clock's cycle. The setting of device address pins for phase position is described above, in the pinstrap configuration section. The INTERLEAVE command is used to set each

device's phase position relative to the group number, number of devices in the group and the specific device's number within the group. Refer to the PMBus specification: "*PMBus Power System Management Protocol Specification; Part II – Command Language.*" The command allows for 16 positions of phase settings resulting in 22.5° increments.

Refer to Zilker Labs Application Note AN2013 for a complete description of the USER_CONFIG and MFR_CONFIG commands.

References

- [1] *ZL2005 Data Sheet*, Zilker Labs, Inc., 2005.
- [2] AN2013 – *ZL2005 and PMBus™*, Zilker Labs, Inc., 2005.

Revision History

Date	Rev. #	
June 28, 2006	1.4	Initial release
May 4, 2009	AN2024.0	Assigned file number AN2024 to app note as this will be the first release with an Intersil file number. Replaced header and footer with Intersil header and footer. Updated disclaimer information to read "Intersil and it's subsidiaries including Zilker Labs, Inc." No changes to app note content.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.

1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.

No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.

17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338