

# シリアル (I<sup>2</sup>C, SPI) EEPROM 発注型名

**R1E X 24 064 A SA S0 I #U0**

Renesas EEPROM

Operating Voltage  
**X : 1.8 to 5.5V**  
 V : 2.5 to 5.5V

Interface  
**24 : I<sup>2</sup>C**  
 25 : SPI

Memory density  
 002 : 2Kbit  
**064 : 64Kbit**  
 512 : 512Kbit

Generation  
**A : A mask**  
 B : B mask

Package type  
**SA : SOP-8pin**  
 TA : TSSOP-8pin

Function  
**I<sup>2</sup>C : S0**  
 SPI : 00

Operating Temperature  
 I : Industrial (-40 to 85 deg.C)

**#U0 : Embossed tape(Pb free·Halogen free)**  
**#K0 : Embossed tape(Pb free·Halogen free)**  
**#S0 : Embossed tape(Pb free)**

	Embossed tape size (pcs/reel)	
	SOP-8pin	TSSOP-8pin
<b>U0</b>	<b>2,500</b>	<b>3,000</b>
<b>K0</b>	<b>4,000</b>	<b>5,000</b>
<b>S0</b>	<b>2,500</b>	<b>3,000</b>

# パラレル EEPROM 発注型名

