






■ ■
■ ■


■







DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILLIMETERS				
FIGURE	SIZE	TOLERANCE	PLATED	QTY
•	0.15	+0.0/-0.0	PLATED	635
•	0.2	+0.0/-0.0	PLATED	11
1	0.55	+0.0/-0.0	PLATED	4
□	0.65	+0.0/-0.0	PLATED	10
□	0.9	+0.0/-0.0	PLATED	32
○	1.1	+0.15/-0.0	NON-PLATED	2
○	2.1	+0.0/-0.0	NON-PLATED	1
⊖	2.5x0.7	+0.0/-0.0	PLATED	2



* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.03 MM

* DIELECTRIC - FR-4 0.36 MM

L2: INT_1 PLANE - COPPER 0.03 MM

* DIELECTRIC - FR-4 0.71 MM

L3: INT_2 CONDUCTOR - COPPER 0.03 MM




* DIELECTRIC - FR-4 0.36 MM


L4: BOTTOM CONDUCTOR - COPPER 0.03 MM
* SURFACE - AIR 0 MM


DESIGN CROSS SECTION CHART
TOTAL THICKNESS 1.55 MM



CUTOUT FOR
USB
CONNECTOR







• •

• •



• • • • •

• • • • •

• • • • •

• • • • •

—

—



