

FS1025

Liquid Flow Sensor Module

The FS1025 liquid flow sensor module measures the flow rate using the thermo-transfer (calorimetric) principle.

The FS1025 offers key advantages over resistorbased flow solutions. The sensor uses thermopile sensing, which provides an excellent signal-to-noise ratio. The sensor comprises a "solid" thermal isolation technology with protective coating.

The non-linear flow output curve allows for sensitivity from low to full-scale flow rates. The FS1025 provides analog output.

FS1025 Module Picture



Features

- Liquid flow: 0 to 7 liters/min (with water)
- Robust "solid" isolation technology
- Resistant to vibration and pressure shock
- Minimal flow resistance
- Analog voltage output
- Supply voltage: 5V

Applications

- Water dispensers
- Liquid metering or switch
- Process controls and monitoring



Contents

| 1. | Pin li | nformation | . 3 |
|----|--------|----------------------------------|-----|
| | 1.1 | Pin Assignments | . 3 |
| | 1.2 | | |
| 2. | Spec | ifications | . 4 |
| | 2.1 | Absolute Maximum Ratings | . 4 |
| | 2.2 | Recommended Operating Conditions | . 4 |
| | 2.3 | Electrical Characteristics | . 4 |
| 3. | Туріс | cal Flow Graphs | . 5 |
| | 3.1 | Heater Enable | |
| | 3.2 | Electrical Connector | |
| | 3.3 | Module Material | |
| | 3.4 | Tubing Guidance | . 6 |
| 4. | Pack | age Outline Drawings | . 6 |
| 5. | Orde | ring Information | . 6 |
| 6. | Revis | sion History | . 6 |

1. Pin Information

1.1 Pin Assignments




Figure 1. FS1025 Pin Assignments - Top View

1.2 Pin Descriptions

| Pin Number | Pin Name | Туре | Description | |
|------------|----------|------|--------------------------------|--|
| 1 | VDD | In | Supply voltage. | |
| 2 | GND | In | Ground. | |
| 3 | OUTPUT | Out | Flow analog output. | |
| 4 | NC | - | - Do not connect. [1] | |
| 5 | HE | In | Heater enable, connect to +5V. | |
| 6 | TEMP | Out | Thermistor analog output. | |

^{1. &}quot;NC" stands for not connected / no connection required / not bonded.

2. Specifications

2.1 Absolute Maximum Ratings

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions can adversely impact product reliability and result in failures not covered by warranty.

| Symbol | Parameter | Conditions | Minimum | Maximum | Unit |
|---|---------------------------|------------|---------|-----------|------|
| V _{IN} | Supply Voltage | - | 5 | 5.5 | V |
| T _{STOR} | Storage Temperature | - | 0 | 85 | °C |
| V _{PIN} | Voltage on All Other Pins | - | -0.3 | VCC + 0.3 | V |
| I _{PIN} | Input Current on Any Pin | - | -80 | 80 | mA |
| ESD Human Body Model | | - | - | 2.5 | kV |
| ESD _{CDM} ESD Charged Device Model | | - | - | 750 | V |

2.2 Recommended Operating Conditions

| Symbol | Parameter | Minimum | Typical | Maximum | Unit |
|-------------------|--|---------|---------|---------|------|
| V _{IN} | Supply Voltage | | 5 | 5.5 | V |
| Т _{АМВ} | Ambient Operating Temperature (in air) | 0 | - | 70 | °C |
| P _{STAT} | Static Pressure | | - | 30 | PSI |

2.3 Electrical Characteristics

| Symbol | Parameter | Conditions | Minimum | Typical | Maximum | Unit |
|-------------------|------------------------|-------------------------------------|---------|---------|---------|---------------|
| I _{VIN} | Current Consumption | - | - | 18 | 20 | mA |
| F _{LQ} | Liquid Flow Range | Tested with water, room temperature | 0 | - | 7 | Liter/ min |
| V _{AOUT} | Analog Voltage Output | Non-linear curve | 0 | - | 5 | V |
| V _{NULL} | Flow Null Voltage | No flow | - | 0.005 | - | ٧ |
| $	au_{H}$ | Flow Response Time [1] | - | - | 5 | - | msec |
| V_{TEMP} | Temperature Output | At 5°C | - | 4.25 | - | V |
| V TEMP | | At 80°C | - | 1.0 | - | V |

^{1.} The flow response time includes a 10% to 90% rise time for the flow sensor to electrically respond to any flow change. Measurements may be affected by the pneumatic interface.

3. Typical Flow Graphs

Figure 2 show the typical analog output versus flow (with water). From a flow rate of 1 to 7 SLPM, the voltage output can be correlated by the following approximation:

Flow rate (liters/min) = $0.2 * (V_{OUT})^2 + 0.3 * (V_{OUT}) + 0.5$




Figure 2. Analog Output Curve (in Water, Room Temperature)

3.1 Heater Enable

The FS1025 allows power savings through the operation of the Heater Enable (HE) pin. The flow sensor element includes a micro-heater. The HE pin powers the micro-heater. When a measurement is taken, the HE pin must be powered on and connected to +5VDC. To conserve power, the HE pin can be pulsed on when taking measurements or grounded (turned off) when no measurements are required. Alternatively, the HE pin can be constantly powered on.

3.2 Electrical Connector

A 6-position receptacle (not provided) is required to mate to the board crimp style connector. A part number example is PHR-6 (JST).




Figure 3. Receptacle Drawing

3.3 Module Material

The wetted contact surface of the FS1025 consists of the following:

- Housing Polyphenylene Ether (PPE) + Polystyrene (PS) blend resin
- Flow Sensor Silicon-carbide thin film
- Epoxy
- Gasket Silicone
- Substrate Gold plating

3.4 Tubing Guidance

The FS1025 module has barb tube endings. Soft tubing with a nominal 7/16-inch (11.1mm) internal diameter is recommended for use. A clamp may be necessary to secure the tubing over the barb.

4. Package Outline Drawings

The package outline drawings are located at the end of this document and are accessible from the Renesas website. The package information is the most current data available and is subject to change without revision of this document.

5. Ordering Information

| Part Number | Package Description | Carrier Type | Temperature Range |
|-------------|---|--------------|-------------------|
| FS1025 | 0 to 7 liter/min liquid flow sensor module with analog voltage output (see MOD01) | Tray | 0° to +70°C |

Revision History


| Revision Date | | Description |
|---------------|-------------|--|
| 1.02 | May 3, 2023 | Added maximum pin ratings to Absolute Maximum Ratings. |
| 1.01 | Sep 2, 2022 | Updated reference output with water. |
| 1.00 | Jul 2, 2021 | Initial release. |



FS1025 Package Outline Drawing

60.0 x 31.5 mm Module

MOD0D1, PSC-4742-01, Rev 00, Page 1



IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.