

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

---

# H8/300H Tiny Series

## Dedicating an I/O Port for Output

---

### Introduction

This document describes how to connect an LED to P11 and light the LED at any interval.

### Target Device

H8/300H Tiny Series H8/3664

### Contents

1. Specifications .....	2
2. Description of Functions .....	3
3. Description of Operation .....	4
4. Description of Software .....	5
5. Flowchart.....	6
6. Program Listing.....	8

### 1. Specifications

- As shown in Figure 1, connect an LED to P11.
- When P11 is set to 1, the LED lights. When P11 is set to 0, the LED is extinguished.





Figure 1 Example of Connecting an LED to an I/O Pin

## 2. Description of Functions

This task describes how to connect an LED to P11 and light or extinguish the LED based on the output of P11. Figure 2 shows the block diagram of the I/O port.

- Port control register 1 (PCR1)  
Used to select the function of the pin of port 1 between input and output bit by bit. In this task, P11 is set to an output port.
- Port data register 1 (PDR1)  
Port 1 is the I/O port data register. In this task, it stores the output data.



**Figure 2 Block Diagram of an I/O Port**

Table 1 shows the details about each function of the registers. The functions (registers) allow the LED to be lit or extinguished based on the output of P11.

**Table 1 Details about the Functions**

Register	Description
PCR1	Used to set P11 as an output port.
PDR1	Stores the value for P11.

### 3. Description of Operation

Figure 3 shows the operation. As shown in Figure 3, the LED is lit or extinguished as determined by the output of P11.




Figure 3 Operation

## 4. Description of Software

### 4.1 About the module

Table 2 lists the module used in this document.

**Table 2 Description about the Module**

Module	Label	Description
Main routine	main	Sets port 1, and lights or extinguishes the LED based on the setting of P11.

### 4.2 About the Arguments

No arguments are used in this document.

### 4.3 About the Registers

The following registers are used in this document.

- PCR1 (port control register 1) address: H'FFE4

Bit	Bit name	Set value	Description
1	PCR11	1	Used to select the function of P11 between input and output. PCR11 = 0: P11 functions as an input port. PCR11 = 1: P11 functions as an output port.

- PDR1 (port data register 1) address: H'FFD4

Bit	Bit name	Set value	Description
1	P11	1	Output data P11 = 0: P11 is set to "Low". P11 = 1: P11 is set to "High".

### 4.4 About RAM


Table 3 shows how RAM is used in this document.

**Table 3 Description about RAM**

Label	Description	Required memory size	Used by:
ram_cnt	Stores the interval of lighting or extinguishing the LED.	One byte	Main routine

5. Flowchart

5.1 Main routine



- Specified Link Addresses

<b>Section</b>	<b>Address</b>
CV1	H'0000
P	H'0100
B	H'FB80

## 6. Program Listing

```

/*****/
/*
/* H8/300HN Series -H8/3664-
/* Application Note
/*
/* 'I/O output'
/*
/* Function
/* : I/O Port
/*
/*
/* External Clock : 16MHz
/* Internal Clock : 16MHz
/* Sub Clock      : 32.768kHz
/*
/*****/

#include <machine.h>

/*****/
/* Symbol Definition
/*****/
struct BIT {
    unsigned char  b7:1;      /* bit7 */
    unsigned char  b6:1;      /* bit6 */
    unsigned char  b5:1;      /* bit5 */
    unsigned char  b4:1;      /* bit4 */
    unsigned char  b3:1;      /* bit3 */
    unsigned char  b2:1;      /* bit2 */
    unsigned char  b1:1;      /* bit1 */
    unsigned char  b0:1;      /* bit0 */
};

#define PCR1_BIT    (*(struct BIT *)0xFFE4)    /* Port Control Register 1    */
#define PCR11       PCR1_BIT.b1               /* Port Control Register 11   */
#define PDR1_BIT    (*(struct BIT *)0xFFD4)    /* Port Data Register 1       */
#define P11         PDR1_BIT.b1               /* Port 11                     */

/*****/
/* Function define
/*****/
void main ( void );

/*****/
/* Ram define
/*****/
unsigned long ram_cnt;    /* RAM area */

/*****/
/* Vector Address
/*****/
#pragma section V1    /* VECTOR SECTION SET */
void (*const VEC_TBL1[])(void) = {

```

```
main
};

#pragma entry main(sp=0xFF80)
#pragma section /* P */
/*****/
/* Main Program */
/*****/
void main ( void )
{
    unsigned long i;

    set_ccr(0x80); /* Initialize CCR/Interrupt Disable */

    PCR11 = 1; /* P11 set output port */
    P11 = 1;
    ram_cnt = 5000000;

    while(1){
        for(i=0; i<ram_cnt; i++){

            P11 = ~P11; /* P11 switching of High and Low */
        };
    }
}
```

### Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Dec.20.03	—	First edition issued

### Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

### Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.