Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.



Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights
 of third parties by or arising from the use of Renesas Electronics products or technical information described in this document.
 No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights
 of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



M61538FP

6-Channel Electronic Volume

REJ03F0103-0100Z Rev.1.0 Mar.23.2004

Description

The M61538FP is 6ch electronic volume. This IC is controlled by 2-wire serial bus and is suitable for Home Audio System.

Features

- Electronic Volume 0 to −95dB, −∞/1dBstep 6-Channel independent Electronic Volume
- MUC I/F Controlled by serial data from microcomputer
- Low Noise $0.85\mu Vrms$: typ. [Volume = 0dB, Rg = 0Ω , IHF-A]
- Low Distortion 0.0012%: typ. [Vi:0.3Vrms, f:1kHz, BW:400Hz to 30kHz]
- Power Supply ±Power supplies or Single power supply

Applications

• Receiver, AV Amp, Mini Stereo etc.

Recommended Operating Condition


- Supply Voltage Range
 - ±Power supplies VCC: +4.5 to +7.5V [Typ: 7V], VEE: -4.5 to -7.5V[Typ: -7V],

DVDD: +2.7 to + 5.5 V [Typ:5V]


— Single power supply VCC: +9 to +12V[Typ: 10V], DVDD: 4.5 to +5.5V[Typ: 5V]

System Block Diagram

(±Power supplies used)



Block Diagram and Pin Configuration



Pin Description

(±Power supplies used)

PIN No.	Name	Function
1, 23	AGND	Analog ground of SW/SL/SR volume
2	SROUT	Output pin of SR channel
3	SLOUT	Output pin of SL channel
4	SWOUT	Output pin of SW channel
5	DVDD	Digital Power supply (Typ: 5V)
6, 7	DATA, CLOCK	Input pin of Control data/clock
8	DGND	Digital ground
9	COUT	Output pin of C channel
10	ROUT	Output pin of R channel
11	LOUT	Output pin of L channel
12, 14	AGND	Analog ground of L/R/C volume
13	LIN	Input pin of L channel
15	RIN	Input pin of R channel
16, 21	AGND	Analog ground of all channels
17	CIN	Input pin of C channel
18	VCC	Positive Power supply (Typ: +7V)
19	VEE	Negative Power supply (Typ: –7V)
20	SWIN	Input pin of SW channel
22	SLIN	Input pin of SL channel
24	SRIN	Input pin of SR channel


M61538FP

Absolute Maximum Ratings

Parameter	Symbol	Ratings	Unit	Condition
Analog Power supply	VCC-VEE	16	V	VCC-VEE (±Power supplies used)
Digital Power supply	DVDD-DGND	7	V	DVDD-DGND
Power dissipation	Pd	1.0	W	Ta ≤ 25°C
Thermal derating	K	10.0	mW/°C	Ta > 25°C
Operating temperature	Topr	-20 to +75	°C	
Storage temperature	Tstg	-40 to +125	°C	

Note: $VEE \le DGND < DVDD \le VCC$

Thermal Deratings (Maximum Rating)



Recommended Operating Conditions


 $(Ta = 25^{\circ}C, unless otherwise noted)$

			Limits			
Parameter	Symbol	Min	Тур	Max	Units	Conditions
Analog supply voltage (Positive)	VCC	4.5	7	7.5	V	±Power supplies used
Analog supply voltage (Negative)	VEE	-7.5	- 7	-4.5	V	±Power supplies used
Analog supply voltage	VCC	9	10	12	V	Single power supply used
Digital supply voltage	VDD	2.7	5	5.5	V	±Power supplies used, DGND = 0V
Digital supply voltage	VDD	4.5	5	5.5	V	Single power supply used, DGND = 0V
Logic "H" level input voltage	VIH	DVDD ×0.7	_	DVDD	V	DGND = 0V
Logic "L" level input voltage	VIL	DGND	_	DVDD ×0.3	V	DGND = 0V


Notes: 1. VEE ≤ DGND < DVDD ≤ VCC

2. Apply VCC, VEE and DVDD at the same time.

Relationship between Data and Clock



Clock and Data Timings




Timing Definition of Digital Block

			Limits		
Parameter	Symbol	Min	Тур	Max	Units
CLOCK cycle time	tcr	8	_	_	
CLOCK pulse width ("H" level)	tWHC	3.2	_	_	<u>.</u>
CLOCK pulse width ("L" level)	tWLC	3.2	_	_	<u>.</u>
Rising time of clock and data	tr	_	_	0.8	<u>.</u>
Falling time of clock and data	tf	_	_	0.8	μs
DATA setup time (Rising time of clock)	tSHD	1.6	_	_	<u>.</u>
DATA setup time (Falling time of clock)	tSLD	1.6	_	_	<u>.</u>
DATA hold time ("H" level)	tHHD	1.6	_	_	
DATA hold time ("L" level)	tHLD	1.6	_	_	

Power on Reset

This IC built-in the power on reset function.

The voltage of DVDD (5 pin) -DGND (8 pin) less than 2.6V, the serial DATA can not accept.



Data Control Specification

Three types of input format can be selected by changing the D14/D15 slot setting status.

(Initialize all data of the 3 formats when power supply (DVDD) turn on.)

(1)	D0a	D1a	D2a	D3a	D4a	D5a	D6a	D7a	D8a	D9a	D10a	D11a	D12a	D13a	D14	D15
		L Channel volume						R Channel volume					0	0		
(2)	D0b	D1b	D2b	D3b	D4b	D5b	D6b	D7b	D8b	D9b	D10b	D11b	D12b	D13b	D14	D15
		C Channel volume						SW Channel volume						0	1	
(3)	D0c	D1c	D2c	D3c	D4c	D5c	D6c	D7c	D8c	D9c	D10c	D11c	D120	D13c	D14	D15
		SL Channel volume					SR Channel volume						1	0		
(4)	D0c	D1c	D2c	D3c	D4c	D5c	D6c	D7c	D8c	D9c	D10c	D11c	D120	D13c	D14	D15
	Test Mode									1	1					

Setting Code

L/R/C/SW/SL/SR Channel Volume

It's initial setting when DVDD turn on.

L/R/C/	L/R/C/SW/SL/SR Channel Volume							It's initial setting when DVDD turn on.							
L	D0a	D1a	D2a	D3a	D4a	D5a	D6a	L	D0a	D1a	D2a	D3a	D4a	D5a	D6a
R	D7a	D8a	D9a	D10a	D11a	D12a	D13a	R	D7a	D8a	D9a	D10a	D11a	D12a	D13a
С	D0b	D1b	D2b	D3b	D4b	D5b	D6b	С	D0b	D1b	D2b	D3b	D4b	D5b	D6b
sw	D7b	D8b	D9b	D10b	D11b	D12b	D13b	sw	D7b	D8b	D9b	D10b	D11b	D12b	D13b
SL	D0c	D1c	D2c	D3c	D4c	D5c	D6c	SL	D0c	D1c	D2c	D3c	D4c	D5c	D6c
SR	D7c	D8c	D9c	D10c	D11c	D12c	D13c	SR	D7c	D8c	D9c	D10c	D11c	D12c	D13c
0dB	0	0	0	0	0	0	0	-48dB	0	1	1	0	0	0	0
-1dB	0	0	0	0	0	0	1	-49dB	0	1	1	0	0	0	1
-2dB	0	0	0	0	0	1	0	-50dB	0	1	1	0	0	1	0
-3dB	0	0	0	0	0	1	1	-51dB	0	1	1	0	0	1	1
-4dB	0	0	0	0	1	0	0	-52dB	0	1	1	0	1	0	0
-5dB	0	0	0	0	1	0	1	-53dB	0	1	1	0	1	0	1
-6dB	0	0	0	0	1	1	0	-54dB	0	1	1	0	1	1	0
-7dB	0	0	0	0	1	1	1	-55dB	0	1	1	0	1	1	1
-8dB	0	0	0	1	0	0	0	-56dB	0	1	1	1	0	0	0
-9dB	0	0	0	1	0	0	1	-57dB	0	1	1	1	0	0	1
-10dB	0	0	0	1	0	1	0	-58dB	0	1	1	1	0	1	0
-11dB	0	0	0	1	0	1	1	-59dB	0	1	1	1	0	1	1
-12dB	0	0	0	1	1	0	0	-60dB	0	1	1	1	1	0	0
-13dB	0	0	0	1	1	0	1	-61dB	0	1	1	1	1	0	1
-14dB	0	0	0	1	1	1	0	-62dB	0	1	1	1	1	1	0
-15dB	0	0	0	1	1	1	1	-63dB	0	1	1	1	1	1	1
-16dB	0	0	1	0	0	0	0	-64dB	1	0	0	0	0	0	0
-17dB	0	0	1	0	0	0	0	-65dB	1	0	0	0	0	0	1
-18dB		0		0	0		1	-66dB			0	0	0	1	0
-19dB -20dB	0	0	1	0	1	0	0	-67dB -68dB	1	0	0	0	1	0	0
-20dB	0	0	1	0	1	0	1	-69dB	1	0	0	0	1	0	1
-21dB	0	0	1	0	1	1	0	-70dB	1	0	0	0	1	1	0
-23dB	0	0	1	0	1	1	1	-71dB	1	0	0	0	1	1	1
-24dB	0	0	1	1	0	0	0	-72dB	1	0	0	1	0	0	0
-25dB	0	0	1	1	0	0	1	-73dB	1	0	0	1	0	0	1
-26dB	0	0	1	1	0	1	0	-74dB	1	0	0	1	0	1	0
-27dB	0	0	1	1	0	1	1	-75dB	1	0	0	1	0	1	1
-28dB	0	0	1	1	1	0	0	-76dB	1	0	0	1	1	0	0
-29dB	0	0	1	1	1	0	1	-77dB	1	0	0	1	1	0	1
-30dB	0	0	1	1	1	1	0	-78dB	1	0	0	1	1	1	0
-31dB	0	0	1	1	1	1	1	-79dB	1	0	0	1	1	1	1
-32dB	0	1	0	0	0	0	0	-80dB	1	0	1	0	0	0	0
-33dB	0	1	0	0	0	0	1	-81dB	1	0	1	0	0	0	1
-34dB	0	1	0	0	0	1	0	-82dB	1	0	1	0	0	1	0
-35dB	0	1	0	0	0	1	1	-83dB	1	0	1	0	0	1	1
-36dB	0	1	0	0	1	0	0	-84dB	1	0	1	0	1	0	0
-37dB	0	1	0	0	1	0	1	-85dB	1	0	1	0	1	0	1
-38dB	0	1	0	0	1	1	0	-86dB	1	0	1	0	1	1	0
-39dB	0	1	0	0	1	1	1	-87dB	1	0	1	0	1	1	1
-40dB	0	1	0	1	0	0	0	-88dB	1	0	1	1	0	0	0
-41dB	0	1	0	1	0	0	1	-89dB	1	0	1	1	0	0	1
-42dB	0	1	0	1	0	1	0	-90dB	1	0	1	1	0	1	0
-43dB	0	1	0	1	0	1	1	-91dB	1	0	1	1	0	1	1
-44dB	0	1	0	1	1	0	0	-92dB	1	0	1	1	1	0	0
-45dB	0	1	0	1	1	0	1	-93dB	1	0	1	1	1	0	1
-46dB	0	1	0	1	1	1	0	-94dB	1	0	1	1	1	1	0
-47dB	0	1	0	1	1	1	1	-95dB	1	0	1	1	1	1	1
								- dB	1	1	1/0	1/0	1/0	1/0	1/0

Electrical Characteristics (Supply current)

(Unless otherwise noted, $Ta = 25^{\circ}C$, VCC(18pin) = 7V, VEE(19pin) = -7V, DVDD(5pin) = 5V, $RL = 10k\Omega$)

Limits **Parameter Symbol** Min Тур Max Units **Test Condition** Positive Supply current ICC 11 20 mΑ when no signal is provided Negative Supply current IEE -20 -11 $\mathsf{m}\mathsf{A}$ when no signal is provided IDD 0.5 2 Digital Supply current $\mathsf{m}\mathsf{A}$ when no signal is provided


Electrical Characteristics (Input/Output)

 $(Unless \ otherwise \ noted, \ Ta=25^{\circ}C, \ VCC(18pin)=7V, \ VEE(19pin)=-7V, \ DVDD(5pin)=5V, \ f=1kHz, \ RL=10k\Omega)$

		_	Limits	_		_
Parameter	Symbol	Min	Тур	Max	Units	Test Condition
Input resistance	Rin	17	25	33	kΩ	13, 15, 17, 20, 22, 24pin, Volume = 0 to -∞dB
Maximum output voltage	VOM	4.0	4.5	_	Vrms	2, 3, 4, 9, 10, 11pin output, RL = 10kΩ, THD = 1%
Pass gain	Gv	-2	0	2	dB	13, 15, 17, 20, 22, 24pin input, 2, 3, 4, 9, 10, 11pin output
Distortion	THD	_	0.0012	0.009	%	BW = 400Hz to 30kHz, Vi = 0.3Vrms, RL=10k Ω
Output noise voltage	Vno	_	0.85	8	μVrms	Volume = 0dB , Rg = 0 , IHF-A
Maximum attenuation	ATTmax	_	-120	-70	dB	Vi = 2Vrms, Volume = -∞dB, IHF-A
Volume gain between channels	Dvol	-1	0	1	dB	Volume = 0, IHF-A
Cross talk between channels	СТ	_	-110	-70	dB	$Vi = 2Vrms, RL = 10k\Omega, IHF-A, Rg = 0\Omega$


Application Example 1

(±Power supplies used)




Application Example 2

(Single power supply used)



Package Dimensions



Renesas Technology Corp. sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.

Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

- Notes regarding these materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.

 2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.

 3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.

 The information described here may contain technical inaccuracies or typographical errors.

 Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.

 Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (http://www.renesas.com).

 4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.

 5. Renesas Technology Corp. semiconductors are not designed or manufactured for

- use.

 6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.

 7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.

 Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.

 8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



RENESAS SALES OFFICES

http://www.renesas.com

Renesas Technology America, Inc. 450 Holger Way, San Jose, CA 95134-1368, U.S.A Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbHDornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd. 7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd. FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd. 26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632 Tel: <65> 6213-0200, Fax: <65> 6278-8001