



RISC-V 32-BIT MCU

RENESAS R9A02G021 GROUP

32-Bit General Purpose MCUs Based on Renesas RISC-V CPU Core

The R9A02G021 ultra-low power 48 MHz MCU series incorporates the energy-efficient, innovative Renesas RISC-V 32-bit core that is particularly well-suited for cost-sensitive and low-power applications. It features 128 KB code flash memory, 4 KB data flash, 16 KB SRAM with ECC support, multiple timers and serial connectivity interfaces, a number of IOs with output current control and rich analog functionality to support a range of general purpose applications. The devices support 125°C temperature operation and are available in 16-pin WLCSP, as well as 24-, 32- and 48-pin QFN package options. Renesas provides a license-free, complete development ecosystem including e²Studio IDE, code generator, compiler toolchain, flashing tools and application notes to assist in developing and deploying this new technology in end systems. Additional commercial environments such as IAR Embedded Workbench and SEGGER Embedded Studio are available for these MCUs.




Target Applications

- Consumer electronics
- Home appliances and accessories
- Industrial sensors and modules, bus-powered sensors
- Health and fitness trackers
- Remote controls
- Battery-powered applications

Key Features

- State-of-the-art 32-bit RISC-V CPU core with high computing power at 48 MHz operation
- Future-proof memory roadmap up to 512/64/16 KB flash/ram/data flash
- Rich analog and digital peripheral mix
- WLCSP and QFN package options
- Low voltage and low power operation, low active current
- Easy-to-use with simple configuration and optimized software generation for small memory footprint

Block Diagram



RENESAS R9A02G021 GROUP

Tools and Support

The e² studio IDE integrates an intuitive Smart Configurator tool that provides device setup and intelligent code generation to make programming and debugging easier and faster. Renesas RISC-V MCUs are also supported by both IAR Embedded Workbench and SEGGER Embedded Studio in conjunction with a standalone version of Smart Configurator.


| IDE | Renesas e ² studio | IAR Embedded Workbench for RISC-V | SEGGER Embedded Studio for RISC-V |
|-----------------------|---|---|-----------------------------------|
| Compiler | • LLVM | • IAR RISC-V Compiler | • SEGGER RISC-V compiler |
| Debug Probe | • Renesas E2/E2 Lite • SEGGER J-Link | • IAR I-Jet • SEGGER J-Link gdb-server | • SEGGER J-Link |
| Production Programmer | • Renesas PG-FP6 • SEGGER J-Flash • Partner solutions | | |

Evaluation Kit

FPB-R9A02G021 Fast Prototyping Board

The R9A02G021 Fast Prototyping Board provides an easy entry point for evaluation, prototyping and development with the R9A02G021 RISC-V MCU. As the board incorporates an emulator circuit, developers can use it for designing their applications without further investments in tools. This board includes through-holes for pin headers allowing access to all MCU signal pins for easy prototyping with a breadboard.

Orderable part number: **RTK9FPG021S00001BJ**



Ordering References

| | | | | | |
|-----------------------|-------|---------------|---------------|---------------|---------------|
| Flash | 128KB | R9A02G0214CNE | R9A02G0214CNH | R9A02G0214CNK | R9A02G0214CBY |
| RAM | 16KB | | | | |
| DataFlash | 4KB | | | | |
| Pin Count | | 48-pin | 32-pin | 24-pin | 16-pin |
| Package | | QFN | QFN | QFN | WLCSP |
| Size (body) | | 7x7mm | 5x5mm | 4x4mm | 1.99x1.99mm |
| Pitch | | 0.5mm | 0.5mm | 0.5mm | 0.4mm |
| Operating Temperature | | -40 to +125°C | -40 to +125°C | -40 to +125°C | -40 to +125°C |

For more details, please visit: renesas.com/r9a02g021

renesas.com

Corporate Headquarters
TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks
Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information
For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/