


# Analog input current vs AVcc (AN0-AN11)

Prepared on Sep. 07, 2007

R8C/26-27 Group  
Topr = 25 degrees C  
AVcc-Vss: 0.1uF Vref-Vss: 0.1uF  
ANIN-Vss: 0.1uF  
AVcc=Vref  
Xin=10MHz φAD=5MHz sample and hold=on Repeat mode

— Analog input = 0V  
— Analog input = AVcc



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.