

## Product Change Notice (PCN)

**Subject:** Datasheet specification change for Listed Intersil ISL68144\* Products

**Publication Date:** 7/7/2017

**Effective Date:** 10/5/2017

**Revision Description:**

Initial Release

**Description of Change:**

This notice is to inform you that Intersil has updated ISL68144\* datasheet. Details regarding the change are contained on the following page.

Product List

ISL68144IRAZ
ISL68144IRAZ-T
ISL68144IRAZ-T7A

**Reason for Change:**

The change aligns the data sheet with the product characteristics and is necessary to maintain product manufacturability in support of customer delivery requirements. Details regarding the change is contained on the following page. For an updated data sheet, please contact your local sales representative or the Intersil Central Application Department via [support@intersil.com](mailto:support@intersil.com). The product brief is available on the Intersil web site at : -

<http://www.intersil.com/content/dam/intersil/documents/isl6/isl68144.pdf>

**Impact on fit, form, function, quality & reliability:**

The change will have no impact on the form, fit, function, quality, reliability and environmental compliance of the devices.

**Product Identification:**

Product affected by this change is identifiable via Intersil's internal traceability system.

**Qualification status:** Not Applicable

**Sample availability:** 7/7/2017

**Device material declaration:** Available upon request

*Questions or requests pertaining to this change notice, including additional data or samples, must be sent to Intersil within 30 days of the publication date.*

For additional information regarding this notice, please contact your regional change coordinator (below)			
Americas: <a href="mailto:PCN-US@INTERSIL.COM">PCN-US@INTERSIL.COM</a>	Europe: <a href="mailto:PCN-EU@INTERSIL.COM">PCN-EU@INTERSIL.COM</a>	Japan: <a href="mailto:PCN-JP@INTERSIL.COM">PCN-JP@INTERSIL.COM</a>	Asia Pac: <a href="mailto:PCN-APAC@INTERSIL.COM">PCN-APAC@INTERSIL.COM</a>

**Appendix A – ISL68144\* Data sheet change (see attached)**

From (page 9 of 47) :

<b>Electrical Specifications</b> Recommended operating conditions, $V_{CC} = 3.3V$ , unless otherwise specified. <b>Boldface limits apply across the operating temperature range -40 °C to +85 °C.</b>					
PARAMETER	TEST CONDITIONS	MIN (Note 7)	TYP	MAX (Note 7)	UNIT
<b><math>V_{CC}</math> SUPPLY CURRENT</b>					
Nominal Supply Current	$V_{CC} = 3.3VDC$ ; $EN1/2 = V_{IH}$ ; $f_{SW} = 400kHz$		63		mA
Shutdown Supply Current	$V_{CC} = 3.3VDC$ ; $EN1/2 = 0V$ , no switching		11.5		mA
<b>VCCS LDO SUPPLY</b>					
Output Voltage		<b>1.20</b>	1.25	<b>1.30</b>	V
Maximum Current Capability	Excluding internal load	<b>50</b>			mA
<b>POWER-ON RESET AND INPUT VOLTAGE LOCKOUT</b>					
$V_{CC}$ Rising POR Threshold			2.7	<b>2.9</b>	V
$V_{CC}$ Falling POR Threshold		<b>1.0</b>			V
Enable (EN0 and EN1) Input High Level			<b>2.3</b>		<b>V</b>

To (page 9 of 47) :

<b>Electrical Specifications</b> Recommended operating conditions, $V_{CC} = 3.3V$ , unless otherwise specified. <b>Boldface limits apply across the operating temperature range -40 °C to +85 °C.</b>					
PARAMETER	TEST CONDITIONS	MIN (Note 7)	TYP	MAX (Note 7)	UNIT
<b><math>V_{CC}</math> SUPPLY CURRENT</b>					
Nominal Supply Current	$V_{CC} = 3.3VDC$ ; $EN1/2 = V_{IH}$ ; $f_{SW} = 400kHz$		63		mA
Shutdown Supply Current	$V_{CC} = 3.3VDC$ ; $EN1/2 = 0V$ , no switching		11.5		mA
<b>VCCS LDO SUPPLY</b>					
Output Voltage		<b>1.20</b>	1.25	<b>1.30</b>	V
Maximum Current Capability	Excluding internal load	<b>50</b>			mA
<b>POWER-ON RESET AND INPUT VOLTAGE LOCKOUT</b>					
$V_{CC}$ Rising POR Threshold			2.7	<b>2.9</b>	V
$V_{CC}$ Falling POR Threshold		<b>1.0</b>			V
Enable (EN0 and EN1) Input High Level		<b>2.55</b>			<b>V</b>
Enable (EN0 and EN1) Input Low Level				<b>0.8</b>	

**Appendix A – ISL68144\* Data sheet change (see attached)**

From (page 11 of 47) :

**Electrical Specifications** Recommended operating conditions,  $V_{CC} = 3.3V$ , unless otherwise specified. **Boldface limits apply across the operating temperature range -40°C to +85°C. (Continued)**

PARAMETER	TEST CONDITIONS	MIN (Note 7)	TYP	MAX (Note 7)	UNIT
<b>SMBus/PMBus</b>					
SALERT, SDA Output Low Level	$I_{OUT} = 4mA$			<b>0.4</b>	V
<b>SCL, SDA Input High/Low Threshold</b>			<b>1.25</b>		<b>V</b>
SCL, SDA Input Hysteresis			2		mV
SCL Frequency Range		<b>0.05</b>		2	MHz

To (page 11 of 47) :

**Electrical Specifications** Recommended operating conditions,  $V_{CC} = 3.3V$ , unless otherwise specified. **Boldface limits apply across the operating temperature range -40°C to +85°C. (Continued)**

PARAMETER	TEST CONDITIONS	MIN (Note 7)	TYP	MAX (Note 7)	UNIT
<b>SMBus/PMBus</b>					
SALERT, SDA Output Low Level	$I_{OUT} = 4mA$			<b>0.4</b>	V
<b>SCL, SDA Input High Level</b>		<b>1.55</b>			<b>V</b>
<b>SCL, SDA Input Low Level</b>				<b>0.8</b>	
SCL, SDA Input Hysteresis			2		mV
SCL Frequency Range		<b>0.05</b>		2	MHz