

Contents

CHAPTER 1	TARGET DEVICES	2
CHAPTER 2	USER'S MANUALS	3
CHAPTER 3	KEYWORDS WHEN UNINSTALLING THE PRODUCT	4
CHAPTER 4	CHANGES	5
4.1	C99 STANDARD LIBRARY FUNCTIONS	5
4.2	ENHANCEMENT OF OUTPUT TO HEX AND BINARY FILES	5
4.3	NEW FACILITY FOR GENERATING VECTOR TABLE SECTIONS SPLIT BY VECTOR TABLE ADDRESS	6
4.4	ENHANCEMENT OF #PRAGMA ADDRESS DIRECTIVE.....	6
4.5	ENHANCEMENT OF #PRAGMA SECTION DIRECTIVE	6
4.6	ENHANCEMENT OF THE FACILITY FOR DETECTING ILLICIT INDIRECT FUNCTION CALLS [PROFESSIONAL EDITION]	6
4.7	ENHANCEMENT OF OPTIMIZATION	6
4.8	RECTIFIED POINT FOR CAUTION	6
4.9	OTHER CHANGES AND IMPROVEMENTS.....	7
CHAPTER 5	POINTS FOR CAUTION	8

Chapter 1 Target Devices

The target devices the CC-RL supports are listed on the Website.

Please see the URL below.

CS+ Product Page:

<https://www.renesas.com/cs+>

Chapter 2 User's Manuals

Please read the following user's manuals along with this document.

Manual Name	Document Number
CC-RL Compiler	R20UT3123EJ0107
CS+ CC-RL Build Tool Operation	R20UT3284EJ0106

Chapter 3 Keywords When Uninstalling the Product

There are two ways to uninstall this product.

- Use the integrated uninstaller from Renesas (uninstalls all CS+ components)
- Use the Windows uninstaller (only uninstalls this product)

To use the Windows uninstaller, select "CS+ CC-RL V1.07.00" from "Programs and Features" of the control panel.

Chapter 4 Changes

This section describes changes to CC-RL from V1.06.00 to V1.07.00.

The features of the latter can only be used if the compiler is registered under the professional license.

They are indicated by [Professional edition] from here on.

4.1 C99 standard library functions

Support for standard library functions of the C99 language has newly been added and functionality for compliance with the C99 standard have been added to existing standard library functions as listed below.

- isblank function
- imaxabs function
- imaxdiv function
- strtimax function
- strtoumax function
- printf function (C99 standard functionality has been added)
- printf_tiny function (C99 standard functionality has been added)
- snprintf function
- sprintf function (C99 standard functionality has been added)
- sprintf_tiny function (C99 standard functionality has been added)
- vprintf function (C99 standard functionality has been added)
- vsnprintf function
- vsprintf function (C99 standard functionality has been added)
- atoll function
- strtod function (C99 standard functionality has been added)
- strtod function (C99 standard functionality has been added)
- strtold function
- strtoll function
- strtoull function
- labs function
- lldiv function

4.2 Enhancement of output to HEX and binary files

The facility for the output of data to HEX and binary files has been enhanced in the following ways.

1. The -crc option is also specifiable when the -form=binary option is specified.

2. A new option `-CHECK_OUTPUT_ROM_AREA` to check whether the addresses of the data output to a HEX file extend beyond the internal ROM or data flash area has been added.
3. The linker option `-output` has been enhanced so that the load address can be specified in an Intel extended HEX format file or a Motorola S-record file to be output. This enhancement allows the output of code for placement at a user-specified address rather than at the address determined during linkage.

4.3 New facility for generating vector table sections split by vector table address

A new option `-SPLIT_VECT` has been added to select the generation of vector table sections split by vector table address. This enables the use of unused areas in vector table sections for other purposes.

4.4 Enhancement of `#pragma` address directive

`#pragma` address can be specified for a variable declared with `__saddr`.

```
<Example>
#pragma address i=0xffe20
int __saddr i;           // An error occurred in CC-RL V1.06.00 and earlier versions.
```

4.5 Enhancement of `#pragma` section directive

In CC-RL V1.06.00 and earlier versions, modifying the section names for string literals, branch tables for switch statements, and initial values for aggregate-type automatic variables from the default names was not possible. In CC-RL V1.07.00, the names can be modified by using the `#pragma` section directive.

4.6 Enhancement of the facility for detecting illicit indirect function calls [Professional edition]

To enhance the facility for detecting indirect function calls to illicit addresses, which was a new facility in CC-RL V1.06.00, the `-cfi_ignore_module` option has been modified to accept library files (*.lib) as parameters.

4.7 Enhancement of optimization

The code generated for the long-type comparison to check for equality to zero has been improved and other optimization items have been enhanced.

4.8 Rectified point for caution

The following point for caution no longer applies. For details, refer to Tool News.

- Point for caution regarding the static variable declaration of an array, structure, or union that has an initializer (CCRL#019)

4.9 Other changes and improvements

The generation of an internal error in response to building has been corrected.

Chapter 5 Points for Caution

Please refer to the user's manual for caution regarding V1.07.00 of the CC-RL compiler.

All trademarks and registered trademarks are the property of their respective owners.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev. 4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.

1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.

No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.

17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338