

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

H8/300H SLP Series

LCD Display Using 1/4 Duty Cycle

Introduction

The segment type LCD controller/driver of the H8/38076R is used for the LCD display by using 1/4 duty cycles.

Target Device

H8/38076R

Contents

| | |
|----------------------------------|----|
| 1. Specifications | 2 |
| 2. Functions Used..... | 3 |
| 3. Principles of Operation | 8 |
| 4. Description of Software | 9 |
| 5. Flowcharts | 12 |

1. Specifications

- The segment-type LCD controller/driver of the H8/38076R is used to perform 1/4 duty drive LCD display.
- A 4-common, 16-segment LCD panel is used. The frame frequency is 64 Hz.
- This sample task displays 8 numeric digits, 01234567, on the LCD panel.
- An external power supply is used to drive the LCD drive power, with 3.0 VDC input to the V1 pin.
- An example of connection between the H8/38076R and the LCD panel is shown in figure 1.




Figure 1 Example of LCD Panel Connection

2. Functions Used

2.1 LCD Controller/Driver Functions

(1) The functions of the LCD controller/driver are described below, and a block diagram of the LCD controller/driver is shown in figure 2.

- LCD port control register (LPCR)

LPCR is an 8-bit readable/writable register that selects duty cycle, and LCD driver and pin function selection.

- LCD control register (LCR)

LCR is an 8-bit readable/writable register that turns on or off the power supply to drive the LCD, activates or halts display function, controls display data, and selects the frame frequency.

- LCD control register 2 (LCR2)

LCR2 is an 8-bit readable/writable register that specifies whether the A waveform or B waveform is used as the LCD drive waveform, selects a step-up clock for use in the 3-V constant voltage power supply circuit, selects whether an LCD power-supply split resistor is disconnected or connected from or to LCD drive power supply, and turns on or off the 3-V constant-voltage power supply.

- Segment output pins (SEG32 to SEG1)

The LCD segment drive pins. All pins are programmable to be used as port pins.

- Common output pins (COM4 to COM1)

The LCD common drive pins. Pins can be used in parallel in 1/2 duty cycle modes.

- LCD power supply pins (V1, V2, V3)

Used when a bypass capacitor is connected externally and when an external power supply is used.

- LCD step-up capacitance pins (C1, C2)

Capacitance pins for connecting the step-up capacitor for the power supply to drive the LCD

- LCD RAM

Used to set display data. The relationship between LCD RAM and display segments differs according to the duty cycle. After the registers necessary for display are set, display is started automatically when data is written to the part corresponding to the duty cycle by means of an instruction in the same way as with ordinary RAM, and the display is turned on. A word or byte access by using the same kind of instruction as for ordinary RAM setting.




Figure 2 Block Diagram of LCD Controller/Driver

(2) This sample task uses 1/4 duty cycles to enable display on the 8-digit LCD panel. The LCD panel segment signals and common signals used in this sample task are shown in figure 3.




Figure 3 LCD Panel Segment Signal and Common Signal Connections

(3) The LCD RAM map for 1/4 duty is shown in figure 4.

| | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| H'F370 | SEG2 | SEG2 | SEG2 | SEG2 | SEG1 | SEG1 | SEG1 | SEG1 |
| H'F371 | SEG4 | SEG4 | SEG4 | SEG4 | SEG3 | SEG3 | SEG3 | SEG3 |
| H'F372 | SEG6 | SEG6 | SEG6 | SEG6 | SEG5 | SEG5 | SEG5 | SEG5 |
| H'F373 | SEG8 | SEG8 | SEG8 | SEG8 | SEG7 | SEG7 | SEG7 | SEG7 |
| H'F374 | SEG10 | SEG10 | SEG10 | SEG10 | SEG9 | SEG9 | SEG9 | SEG9 |
| H'F375 | SEG12 | SEG12 | SEG12 | SEG12 | SEG11 | SEG11 | SEG11 | SEG11 |
| H'F376 | SEG14 | SEG14 | SEG14 | SEG14 | SEG13 | SEG13 | SEG13 | SEG13 |
| H'F377 | SEG16 | SEG16 | SEG16 | SEG16 | SEG15 | SEG15 | SEG15 | SEG15 |
| | ↓ | ↓ | ↓ | ↓ | ↓ | ↓ | ↓ | ↓ |
| | COM4 | COM3 | COM2 | COM1 | COM4 | COM3 | COM2 | COM1 |

Figure 4 LCD RAM Map for 1/4 Duty Cycles

- (4) The relationship between the LCD panel display and LCD RAM set values used in this sample task is shown in Figure 5. Setting LCD RAM as shown in Figure 5 displays "01234567" on the LCD panel.

| | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 | |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|------------------------|
| H'F370 | 0 | 0 | 0 | 1 | 0 | 1 | 1 | 1 | Setting to display "7" |
| H'F371 | 1 | 1 | 1 | 1 | 0 | 1 | 0 | 1 | Setting to display "6" |
| H'F372 | 1 | 0 | 1 | 1 | 0 | 1 | 0 | 1 | Setting to display "5" |
| H'F373 | 0 | 0 | 1 | 1 | 0 | 1 | 1 | 0 | Setting to display "4" |
| H'F374 | 1 | 0 | 1 | 0 | 0 | 1 | 1 | 1 | Setting to display "3" |
| H'F375 | 1 | 1 | 1 | 0 | 0 | 0 | 1 | 1 | Setting to display "2" |
| H'F376 | 0 | 0 | 0 | 0 | 0 | 1 | 1 | 0 | Setting to display "1" |
| H'F377 | 1 | 1 | 0 | 1 | 0 | 1 | 1 | 1 | Setting to display "0" |

Figure 5 Relationship between LCD Display and LCD RAM Set Values

- (5) The relationship of LCD RAM to SEG1 and SEG2 of the LCD panel is shown in Figure 6. When 1 is set in LCD RAM bits corresponding to a through g and P, as shown in Figure 6, the LCD display is turned on, and when 0 is set in these bits, the LCD display is turned off.




Figure 6 Relationship of LCD RAM Set Values and LCD Display/Non-Display

(6) Examples of LCD panel SEG1 and SEG2 display and display data are shown in table 1.

Table 1 Examples of Display Data

| Symbol | Display | Address | Display Data | | | | | | | | |
|--------|---------|---------|--------------|---|---|---|---|---|---|---|-------------|
| | | | Binary | | | | | | | | Hexadecimal |
| 0 | | H'F370 | 1 | 1 | 0 | 1 | 0 | 1 | 1 | 1 | H'D7 |
| 1 | | H'F370 | 0 | 0 | 0 | 0 | 0 | 1 | 1 | 0 | H'06 |
| 2 | | H'F370 | 1 | 1 | 1 | 0 | 0 | 0 | 1 | 1 | H'E3 |
| 3 | | H'F370 | 1 | 0 | 1 | 0 | 0 | 1 | 1 | 1 | H'A7 |
| 4 | | H'F370 | 0 | 0 | 1 | 1 | 0 | 1 | 1 | 0 | H'36 |
| 5 | | H'F370 | 1 | 0 | 1 | 1 | 0 | 1 | 0 | 1 | H'B5 |
| 6 | | H'F370 | 1 | 1 | 1 | 1 | 0 | 1 | 0 | 1 | H'F5 |
| 7 | | H'F370 | 0 | 0 | 0 | 1 | 0 | 1 | 1 | 1 | H'17 |
| 8 | | H'F370 | 1 | 1 | 1 | 1 | 0 | 1 | 1 | 1 | H'F7 |
| 9 | | H'F370 | 1 | 0 | 1 | 1 | 0 | 1 | 1 | 1 | H'B7 |

2.2 Assignment of Functions

Table 2 shows the assignment of functions in this sample task.

Table 2 Assignment of Functions

| Elements | Description |
|--------------|---|
| LPCR | Selects duty cycle, LCD driver, and pin function. |
| LCR | Turns on or off the power supply to drive the LCD, activates or halts display function, controls display data, and selects the frame frequency. |
| LCR2 | Specifies whether the A waveform or B waveform is used as the LCD drive waveform, selects a step-up clock for use in the 3-V constant voltage power supply circuit, selects whether an LCD power-supply split resistor is disconnected or connected from or to LCD drive power supply, and turns on or off the 3-V constant-voltage power supply. |
| LTRMR | Adjusts 3-V constant voltage used for LCD drive power supply |
| COM1 to COM4 | Used as common drivers |
| LCD RAM | Used to set LCD display data |

3. Principles of Operation

The principles of operation of this sample task are illustrated in figure 7. Data is displayed on the LCD panel by writing display data to the LCD RAM after making LCD controller/driver function settings.




Figure 7 Principles of Operation

4. Description of Software

4.1 Modules

Table 3 shows the modules used in this sample task.

Table 3 Modules

| Function Name | Description |
|---------------|--|
| main | Main routine Sets LCD RAM, LCD controller/driver initially, and sets LCD display data |

4.2 Arguments

No arguments are used in this sample task.

4.3 Internal Registers Used

The internal registers used in this sample task are shown below.

- LCD RAM** Addresses: H'F370 to H'F37F
 Function: Automatically starts display when data is written to the corresponding addresses and LCD display is turned on.
 Set value: Undefined
 R/W: R/W

- LPCR** LCD port control register Address: H'FFA0

| Bit | Bit Name | Set Value | R/W | Description |
|-----|----------|-----------|-----|---|
| 7 | DTS1 | 1 | R/W | Duty cycle select 1, 0 |
| 6 | DTS0 | 1 | R/W | Common function select |
| 5 | CMX | 0 | R/W | The combination of DTS1 and DTS0 selects static mode or 1/2 to 1/4 duty cycles. CMX selects either static, 1/2, 1/3, or 1/4 duty cycle. CMX specifies whether or not the same waveform is to be output from multiple pins to increase the common drive power when not all common pins are used because of the duty setting. DTS1 = 1, DTS0 = 1, CMX = -: Duty cycle set to 1/4, COM1 to COM4 set as common drivers |
| 3 | SGS3 | 0 | R/W | Segment driver select 3 to 0 |
| 2 | SGS2 | 1 | R/W | Select segment drivers to be used. |
| 1 | SGS1 | 0 | R/W | SGS3 = 0, SGS2 = 1, SGS1 = 0, SGS0 = 0: SEG1 to SEG16 set as segment drivers |
| 0 | SGS0 | 0 | R/W | |

-: Don't care

• LCR LCD control register Address: H'FFA1

| Bit | Bit Name | Set Value | R/W | Description |
|-----|----------|-----------|-----|---|
| 6 | PSW | 0 | R/W | <p>LCD drive power supply control</p> <p>When LCD display is not necessary in the power-down modes, or when an external power supply is used, the LCD drive power supply can be turned off. When the ACT bit is cleared to 0, or in the standby mode, the LCD drive power supply is turned off regardless of the setting of this bit.</p> <p>0: The LCD drive power supply is turned off 1: The LCD drive power supply is turned on</p> |
| 5 | ACT | 1 | R/W | <p>Display function start</p> <p>Selects whether or not LCD controller/driver is to be used. Clearing this bit to 0 stops LCD controller/driver operation. The LCD drive power supply is turned off regardless in the value of PSW. However, register contents are retained.</p> <p>0: LCD controller/driver stops 1: LCD controller/driver operates</p> |
| 4 | DISP | 1 | R/W | <p>Display data control</p> <p>Selects whether LCD RAM contents are to be displayed, or blank data is to be displayed regardless of LCD RAM contents.</p> <p>0: Blank data is displayed 1: LCD RAM data is displayed</p> |
| 3 | CKS3 | 0 | R/W | Frame frequency select 3 to 0 |
| 2 | CKS2 | 0 | R/W | Selects the operating clock and the frame frequency. |
| 1 | CKS1 | 0 | R/W | CKS3 = 0, CKS2 = -, CKS1 = 0, CKS0 = 1: Operating clock = $\phi_w/2$, frame frequency = 64 Hz (frame frequency when $\phi_w = 32.768$ kHz) |
| 0 | CKS0 | 1 | R/W | |

-: Don't care

- LCR2 LCD control register 2 Address: H'FFA2


| Bit | Bit Name | Set Value | R/W | Description |
|-----|----------|-----------|-----|---|
| 7 | LCDAB | 0 | R/W | Waveform A or B switchover Selects waveform A or waveform B as the LCD drive waveform. 0: Drive using waveform A 1: Drive using waveform B |
| 6 | HCKS | 0 | R/W | 3 V constant-voltage circuit step-up clock select Selects step-up clock used for 3 V constant-voltage circuit. The step-up clock is the clock selected by bits CKS3 to CKS0 of LCR divided by 4 or 8. 0: Step-up clock is LCD clock divided by 4 1: Step-up clock is LCD clock divided by 8 |
| 5 | CHG | 1 | R/W | LCD split-resistance connection control Selects whether the LCD power supply split-register is to be disconnected from or connected to LCD drive power supply. 0: Disconnected 1: Connected |
| 4 | SUPS | 0 | R/W | 3 V constant-voltage power supply control When LCD display is not necessary in power-down modes, or when an external power supply is used, the 3 V constant-voltage power supply can be turned off. 0: Turns off 3-V constant-voltage power supply 1: Turns on 3-V constant-voltage power supply |

4.4 RAM Usage

No RAM is used in this sample task.

5. Flowcharts

5.1 main (Main Routine)



5.2 Link Address Specifications

| Section Name | Address |
|--------------|------------|
| CV1 | H'00000000 |
| P | H'00001000 |

Revision Record

| Rev. | Date | Description | |
|------|-----------|-------------|----------------------|
| | | Page | Summary |
| 1.00 | Sep.16.04 | — | First edition issued |
| | | | |
| | | | |
| | | | |
| | | | |

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.