

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

## **H8/300L**

### **Hardware Interface Technique for Peripherals (HWperh)**

---

#### **Introduction**

This application note aims to describe the critical areas to observe while working with the peripherals of the H8/38024F microcomputer.

The key peripherals focused in this application note are catered mainly for SCI and LCD functions found in the microcomputer.

#### **Target Device**

H8/300L Super Low Power series – H8/38024F

## Contents

1. SCI Interface .....	3
1.1 Asynchronous Mode .....	3
1.2 Synchronous Mode .....	4
1.3 Clock .....	5
1.3.1 Asynchronous Mode .....	5
1.3.2 Synchronous Mode .....	5
1.4 Interrupts .....	6
2. LCD Interface .....	6
2.1 What is frame frequency? .....	7
2.2 What is drive waveform? .....	7
2.3 How to boost the LCD Drive Power? .....	8
2.4 How to operate LCD controller/driver in Power Down Modes .....	8
2.5 Relationships between LCD RAM and Duty Cycle .....	9
2.6 Electrical Characteristic .....	11
2.6.1 Mask or Z-TAT version .....	11
2.6.2 F-ZTAT version .....	11
Reference .....	12
Revision Record .....	13

## 1. SCI Interface

In H8/38024F microcomputer, there is only one serial communication interface, SCI3. It is capable of carrying out either in asynchronous and synchronous mode. It supports full-duplex communication; has an on-chip baud rate generator which allows any desired bit rate to be selected; has a choice of an internal or external clock as the transmit/receive clock source; has six interrupts

It also supports multiprocessor communication function that enables serial data to be transferred among processors.

In this application note, it does not go to the extent to cover the introduction of the various SCI registers and on how to configure as well as access these registers. Instead it would focus on informing the various concerns or consideration when working on the SCI3 such as observing the timing aspect, etc.

### 1.1 Asynchronous Mode

For asynchronous mode, serial data is transferred with synchronization provided character by character. Serial data can be exchanged with standard asynchronous communication LSI receiver/transmitter and such as UART & ACIA. There is a choice of 16 transfer formats.

Data Length	7, 8, 5 bits
Stop bit Length	1 or 2 bits
Parity	Even, Odd, or None
Multiprocessor Bit	1 or 0
Receive Error Detection	Parity, Overrun, and Framing Errors
Break Detection	Break detected by reading the RXD <sub>32</sub> pin level directly when a framing error occurs.




### 1.3 Clock

#### 1.3.1 Asynchronous Mode

Either an internal clock generated by the baud rate generator or an external clock input at the SCK<sub>32</sub> pin can be selected as the SCI3 transmit/receive clock. For selection of the clock source, one has to set the respective registers stated in the hardware manual.

When an external clock is input at the SCK<sub>32</sub> pin, the clock frequency should be 16 times the bit rate.

When SCI3 operates on an internal clock, the clock can be output at the SCK<sub>32</sub> pin. In this case, the frequency of the output clock is the same as the bit rate and the phase is such that the clock rises at the center of each bit of transmit/receive data as shown in the Figure below in asynchronous mode.




#### 1.3.2 Synchronous Mode

Either an internal clock generated by the baud rate generator or an external clock input at the SCK<sub>32</sub> pin can be selected as the SCI3 transmit/receive clock.

When SCI3 operates on an internal clock, the clock can be output at the SCK<sub>32</sub> pin. Eight pulses of the serial clock are output in transmission or reception of a character.

When SCI3 is not transmitting or receiving, the clock is fixed in the high level. Refer to the Figure below for illustration.




Note that when an external clock is used in asynchronous mode, the clock should not be stopped during operation including initialization. When an external clock is used in synchronous mode, the clock should not be supplied during operation including initialization.

## 1.4 Interrupts

SCI3 can generate six kinds of interrupts: transmit ends, transmit data empty, receive data full and three receive error interrupts (overrun error, framing, parity error). These interrupts have the same vector address. For details on the enabling and disabling of the interrupts, refer to the microcomputer hardware manual.

Last but not least, one of the key points worth highlighting here is the receive data sampling timing and receive margin in asynchronous mode. In asynchronous mode, SCI3 operates on a basic clock with a frequency 16 times the transfer rate. When receiving, SCI3 performs internal synchronization by sampling the falling edge of the start bit with the basic clock. Receive data is latched internally at the 8<sup>th</sup> rising edge of the basic clock. This is illustrated in the Figure below.



## 2. LCD Interface

This section aims to address the various concerns when interfacing with a LCD panel using the LCD function of the H8/38024F microcomputer. It does not go further into describing on how to set the various registers.

For H8/38024F microcomputer, it provides an on-chip segment type LCD control circuit, LCD driver, and power supply circuit, enabling it to directly drive a LCD panel. Features of the LCD driver/controller are given below:

- Display capacity

Duty Cycle	Internal Driver
Static	32 seg
1/2	32 seg
1/3	32 seg
1/4	32 seg

- LCD RAM capacity [128bits = 8bits x 16bytes]
- Word Access to LCD RAM
- Capable of parallel connection
- Display possible in all operating modes except standby mode
- Choice of 11 frame frequencies
- Built-in power supply spilt-resistance, supplying LCD drive power
- A or B waveform selectable

## 2.1 What is frame frequency?

The LCD frame frequency is defined as the rate at which the backplane and segment outputs change. The frame frequency is calculated to be the LCD period/2 \* number of backplanes. The range of frame frequencies is from 25 to 250Hz with the most common being between 50 and 150Hz. Higher frequencies result in higher power consumption while lower frequencies cause flicker in the images on the LCD panel. The following table shows the frame frequency selection.

Bit 3 CKS3	Bit 2 CKS2	Bit 1 CKS1	Bit 0 CKS0	Operating Clock	Frame Frequency <sup>*2</sup>	
					$\omega = 2 \text{ MHz}$	$\omega = 250 \text{ kHz}^{*1}$
0	*	0	0	$\omega$	128 Hz <sup>*3</sup> (initial value)	
0	*	0	1	$\omega/2$	64 Hz <sup>*3</sup>	
0	*	1	*	$\omega/4$	32 Hz <sup>*3</sup>	
1	0	0	0	$\omega/2$	—	244 Hz
1	0	0	1	$\omega/4$	977 Hz	122 Hz
1	0	1	0	$\omega/8$	488 Hz	61 Hz
1	0	1	1	$\omega/16$	244 Hz	30.5 Hz
1	1	0	0	$\omega/32$	122 Hz	—
1	1	0	1	$\omega/64$	61 Hz	—
1	1	1	0	$\omega/128$	30.5 Hz	—
1	1	1	1	$\omega/256$	—	—

\*: Don't care


Notes: \*1 This is the frame frequency in active (medium-speed,  $\omega_{osc}/16$ ) mode when  $\omega = 2 \text{ MHz}$ .

\*2 When 1/3 duty is selected, the frame frequency is 4/3 times the value shown.

\*3 This is the frame frequency when  $\omega = 32.768 \text{ kHz}$ .


## 2.2 What is drive waveform?

Two types of waveforms are used to drive LCD panel, namely type A and type B. A LCD driver must maintain a 0 V<sub>DC</sub> across each pixel. Type A waveforms maintain 0 VDC over a single frame whereas type B takes two frames. The following Figure illustrates the different type drive waveforms.



### 2.3 How to boost the LCD Drive Power?

When a large LCD panel is used, the on-chip power supply capacity may be insufficient. If the power supply is insufficient when VCC is used as the power supply, the power supply impedance must be reduced. How do we go about doing it? You can connect a bypass capacitor of value around 0.1uF to 0.3uF to pins V1 to V3 or by adding spilt-resistance externally. This following Figure illustrates the connection of the external spilt-resistance.



### 2.4 How to operate LCD controller/driver in Power Down Modes

In the H8/38024 series, the LCD controller/driver can be operated even in the power-down modes.

Note that in subactive, watch mode and subsleep mode, the system clock oscillator stops and therefore, unless the on-chip subclock is selected, the clock will not be supplied and display will halt. Since there is a possibility that a direct current will be supplied to the LCD panel in this case, it is essential to ensure that subclock is selected. In active(medium-speed) mode, the system clock is enabled, therefore the frame frequency setting must be modified to ensure that the frame frequency does not change. You may refer to the section 2.1 in this application note concerning the frame frequency selection.

Mode		Reset	Active	Sleep	Watch	Sub-active	Sub-sleep	Standby	Module Standby
Clock	ø	Runs	Runs	Runs	Stops	Stops	Stops	Stops	Stops <sup>*1</sup>
	øw	Runs	Runs	Runs	Runs	Runs	Runs	Stops <sup>*1</sup>	Stops <sup>*1</sup>
Display	ACT = 0	Stops	Stops	Stops	Stops	Stops	Stops	Stops <sup>*2</sup>	Stops
operation	ACT = 1	Stops	Functions	Functions	Functions <sup>*3</sup>	Functions <sup>*3</sup>	Functions <sup>*3</sup>	Stops <sup>*2</sup>	Stops

Notes: \*1 The subclock oscillator does not stop, but clock supply is halted.

\*2 The LCD drive power supply is turned off regardless of the setting of the PSW bit.


\*3 Display operation is performed only if øw, øw/2, or øw/4 is selected as the operating clock.

\*4 The clock supplied to the LCD stops.


## 2.5 Relationships between LCD RAM and Duty Cycle

The relationships between the LCD RAM and the display segments differ according to the duty cycle. After setting the registers required for display, data is written to the part corresponding to the duty using the same kind of instruction as for ordinary RAM, and the display is started automatically when turned on. Word- or byte-access instructions can be used for RAM setting.

The following Figures illustrate the relationship between LCD RAM and various duty cycle supported.




LCD RAM Map with 1/4 Duty Cycle




Space not used for display

LCD RAM Map with 1/3 Duty Cycle



LCD RAM Map with 1/2 Duty Cycle



LCD RAM Map with Static Mode

## 2.6 Electrical Characteristic

The electrical characteristic for the LCD controller/driver differs for mask & F-ZTAT version. Product designer has to take note of this difference to ensure correct operation. In addition to this, product designer also has to consult the electrical specification of the LCD panel provided by the LCD manufacturer to ensure that the LCD driver/controller is suitable to drive the LCD panel used.

The followings tables provide the readings for both mask and F-ZTAT version.

### 2.6.1 Mask or Z-TAT version

$V_{CC} = 1.8\text{ V to }5.5\text{ V}$ ,  $AV_{CC} = 1.8\text{ V to }5.5\text{ V}$ ,  $V_{SS} = AV_{SS} = 0.0\text{ V}$ ,  $T_a = -20^\circ\text{C to }+75^\circ\text{C}^{*3}$   
(including subactive mode) unless otherwise specified.

Item	Symbol	Applicable Pins	Test Conditions	Values			Unit	Reference Figure
				Min	Typ	Max		
Segment driver drop voltage	$V_{DS}$	SEG <sub>1</sub> to SEG <sub>32</sub>	$I_D = 2\ \mu\text{A}$ $V_1 = 2.7\text{ V to }5.5\text{ V}$	—	—	0.6	V	*1
Common driver drop voltage	$V_{DC}$	COM <sub>1</sub> to COM <sub>4</sub>	$I_D = 2\ \mu\text{A}$ $V_1 = 2.7\text{ V to }5.5\text{ V}$	—	—	0.3	V	*1
LCD power supply split-resistance	$R_{LCD}$		Between $V_1$ and $V_{SS}$	0.5	3.0	9.0	MΩ	
Liquid crystal display voltage	$V_{LCD}$	$V_1$		2.2	—	5.5	V	*2

Notes: \*1 The voltage drop from power supply pins  $V_1$ ,  $V_2$ ,  $V_3$ , and  $V_{SS}$  to each segment pin or common pin.

\*2 When the liquid crystal display voltage is supplied from an external power source, ensure that the following relationship is maintained:  $V_{CC} \geq V_1 \geq V_2 \geq V_3 \geq V_{SS}$ .

\*3 The guaranteed temperature as an electrical characteristic for Die products is 75°C.

### 2.6.2 F-ZTAT version

$V_{CC} = 2.7\text{ V to }3.6\text{ V}$ ,  $AV_{CC} = 2.7\text{ V to }3.6\text{ V}$ ,  $V_{SS} = AV_{SS} = 0.0\text{ V}$ ,  $T_a = -20^\circ\text{C to }+75^\circ\text{C}^{*3}$   
(including subactive mode) unless otherwise specified.

Item	Symbol	Applicable Pins	Test Conditions	Values			Unit	Reference Figure
				Min	Typ	Max		
Segment driver drop voltage	$V_{DS}$	SEG <sub>1</sub> to SEG <sub>32</sub>	$I_D = 2\ \mu\text{A}$ $V_1 = 2.7\text{ V to }3.6\text{ V}$	—	—	0.6	V	*1
Common driver drop voltage	$V_{DC}$	COM <sub>1</sub> to COM <sub>4</sub>	$I_D = 2\ \mu\text{A}$ $V_1 = 2.7\text{ V to }3.6\text{ V}$	—	—	0.3	V	*1
LCD power supply split-resistance	$R_{LCD}$		Between $V_1$ and $V_{SS}$	0.5	3.0	9.0	MΩ	
Liquid crystal display voltage	$V_{LCD}$	$V_1$		2.2	—	3.6	V	*2

Notes: \*1 The voltage drop from power supply pins  $V_1$ ,  $V_2$ ,  $V_3$ , and  $V_{SS}$  to each segment pin or common pin.

\*2 When the liquid crystal display voltage is supplied from an external power source, ensure that the following relationship is maintained:  $V_{CC} \geq V_1 \geq V_2 \geq V_3 \geq V_{SS}$ .

\*3 The guaranteed temperature as an electrical characteristic for Die products is 75°C.

## Reference

1. H8/38024 Series, H8/38024F-ZTAT™ Hardware Manual
2. [www.embedded.com](http://www.embedded.com)
3. [www.ednmag.com](http://www.ednmag.com)

**Revision Record**

Rev.	Date	Description	
		Page	Summary
1.00	Sep.03	-	First edition issued

Keep safety first in your circuit designs!

1. Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
2. Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.  
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.  
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.  
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.